






2.00(PITCH)




SECTION A-A



技术指标(Technical Index):


- 1.工作温度(Temperature range): $-40^{\circ}\text{C}\sim 125^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):200V DC/AC(rms).
- 3.额定电流(Rated current):2.0A.
- 4.接触电阻(Contact resistance): $\leq 25\text{m}\Omega$.
- 5.耐压值(Withstanding voltage):500V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.



序号	品名	材质
①	PH2.0弯针WTB胶芯	LCP UL94V-0 本色
②	PH2.0弯针WTB端子	铜合金/表面镀锡



DIMENSION IN mm		TOLERANCE UNLESS OTHERWISE SPECIFIED			
.X $\pm$ 0.5	X.* $\pm$ 5°	APR.	Alex	TITLE: PH2.0弯针WTB	
.XX $\pm$ 0.25	.X.* $\pm$ 3°	CHK.	Jack	DWG NO. XY-PH2.0-NA21-BL	
.XXX $\pm$ 0.15	.XX.* $\pm$ 1°	DRA.	Can	PROJ.  CUSTOMER DRAWING	
SIZE A4		SCALE 1:1		SHEET 1/1	REV. A

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd





NOTE(注):


- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
(10片孔距累积公差 $\pm 0.2\text{mm}$.)
- 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
(载带拱/弯MAX:1/100mm.)
- 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
(所有的尺寸要满足协会EIA-481规范.)
- 4.MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING.
(载带材料: 透明防静电 PS, 冷封.)
- 5.THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.50 \pm 0.05\text{mm}$.)
- 6.PACKING LENGTH PER REEL: 7.008 METERS. (每卷包装长度: 7.008米.)
- 7.COMPONENT LOAD PER REEL: 500 PCS. (每卷包装数量: 500只, 每包数量: 550只, 最长17只.)
- 8.纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及纸填充.
- 9.纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.



CKT (2.0mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	16	600	14	8400
3				
4	24	600	10	6000
5				
6				
7				
8	32	600	8	4800
9				
10				
11				
12	44	600	6	3600
13				
14				
15				
16				
17	56	600	5	3000
18				
19				
20				



纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Height (CM)	7.5	15	32



CKT (2.0mm pitch)	B0	W	F	S
2	6.30	16	7.50	
3	8.30			
4	10.30	24	11.50	
5	12.30			
6	14.30			
7	16.30			
8	18.30	32	14.20±0.10	28.40
9	20.30			
10	22.30			
11	24.30			
12	26.30	44	20.20±0.10	40.40
13	28.30			
14	30.30			
15	32.30			
16	34.30			
17	36.30	56	26.20±0.10	52.40
18	38.30			
19	40.30			
20	42.30			

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	.X*± 5°	APR.	Alex	TITLE: PH2.0#WTB	
.XX±0.25	.X*± 3°	CHK.	Jack	DWG NO. XY-PH2.0-NA21-BL	
.XXX±0.15	.XX*± 1°	DRA.	Can	PROJ.  CUSTOMER DRAWING	
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A