


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。	序号
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。	①
3. 额定电压: 125V, AC。	②
4. 接触电阻: $\leq 0.02\Omega$ 。	
5. 绝缘电阻: $\geq 100\text{M}\Omega$	

Part No	CKT	A	B	C	D	E
XY-DF810A-8LBGDW	8	2.40	3.45	5.10	4.20	4.00
XY-DF810A-10LBGDW	10	3.20	4.25	5.90	5.00	
XY-DF810A-12LBGDW	12	4.00	5.05	6.70	5.80	
XY-DF810A-14LBGDW	14	4.80	5.85	7.50	6.60	
XY-DF810A-16LBGDW	16	5.60	6.65	8.30	7.40	
XY-DF810A-18LBGDW	18	6.40	7.45	9.10	8.20	
XY-DF810A-20LBGDW	20	7.20	8.25	9.90	9.00	
XY-DF810A-22LBGDW	22	8.00	9.05	10.70	9.80	
XY-DF810A-24LBGDW	24	8.80	9.85	11.50	10.60	
XY-DF810A-26LBGDW	26	9.60	10.65	12.30	11.40	
XY-DF810A-28LBGDW	28	10.40	11.45	13.10	12.20	8.00
XY-DF810A-30LBGDW	30	11.20	12.25	13.90	13.00	
XY-DF810A-32LBGDW	32	12.00	13.05	14.70	13.80	
XY-DF810A-34LBGDW	34	12.80	13.85	15.50	14.60	
XY-DF810A-36LBGDW	36	13.6	14.65	16.30	15.40	
XY-DF810A-38LBGDW	38	14.40	15.45	17.10	16.20	
XY-DF810A-40LBGDW	40	15.20	16.25	17.90	17.00	
XY-DF810A-44LBGDW	44	16.80	17.85	19.50	18.60	
XY-DF810A-50LBGDW	50	19.20	20.25	21.90	21.00	
XY-DF810A-60LBGDW	60	23.20	24.25	25.90	25.00	
XY-DF810A-70LBGDW	70	27.20	28.25	29.90	29.00	
XY-DF810A-80LBGDW	80	31.20	32.25	33.90	33.00	
XY-DF810A-100LBGDW	100	39.20	40.25	41.90	41.00	

序号	品名	材质
①	0.8 Pitch双排立式 BTB插座胶壳	PA10T UL94 V-0, 颜色:黑色
②	0.8 Pitch双排立式 BTB插座端子	铜合金/表面镀金
③	0.8 Pitch双排立式 BTB插座拨叉	LCP UL94 V-0, 颜色:黑色

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.5	X.*±1*	APR. Alex	TITLE: 0.8 Pitch 0.8 Pitch 0.8 Pitch (精1.0)				
.XX±0.2	.X*±	CHK. Jack	DWG NO. XY-DF810A-NLBGDW				
.XXX±0.1	.XX*±	DRA. Can	PROJ. 		CUSTOMER DRAWING		
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A	