


REV.	Q'TY	ECN. NO.	APR.	DATE


序号	品名	材质
①	0.5 Pitch D型单槽制 插BTB公座胶芯	LCP UL94 V-0,颜色:本色
②	0.5 Pitch D型单槽制 插BTB公座端子	铜合金/表面点镀金



Part No	CKT	A	B	C	D
XY-DF533D-4CJGDW	2*2	0.50	2.50	2.50	1.70
XY-DF533D-6CJGDW	2*3	1.00	3.00	3.00	2.20
XY-DF533D-8CJGDW	2*4	1.50	3.50	3.50	2.70
XY-DF533D-10CJGDW	2*5	2.00	4.00	4.00	3.20
XY-DF533D-12CJGDW	2*6	2.50	4.50	4.50	3.70
XY-DF533D-14CJGDW	2*7	3.00	5.00	5.00	4.20
XY-DF533D-16CJGDW	2*8	3.50	5.50	5.50	4.70
XY-DF533D-18CJGDW	2*9	4.00	6.00	6.00	5.20
XY-DF533D-20CJGDW	2*10	4.50	6.50	6.50	5.70
XY-DF533D-22CJGDW	2*11	5.00	7.00	7.00	6.20
XY-DF533D-24CJGDW	2*12	5.50	7.50	7.50	6.70
XY-DF533D-26CJGDW	2*13	6.00	8.00	8.00	7.20
XY-DF533D-28CJGDW	2*14	6.50	8.50	8.50	7.70
XY-DF533D-30CJGDW	2*15	7.00	9.00	9.00	8.20
XY-DF533D-32CJGDW	2*16	7.50	9.50	9.50	8.70
XY-DF533D-34CJGDW	2*17	8.00	10.00	10.00	9.20
XY-DF533D-36CJGDW	2*18	8.50	10.50	10.50	9.70
XY-DF533D-38CJGDW	2*19	9.00	11.00	11.00	10.20
XY-DF533D-40CJGDW	2*20	9.50	11.50	11.50	10.70
.....	...	...	...	...	...
XY-DF533D-80CJGDW	2*40	19.50	21.50	21.50	20.70

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.5	X.* ± 1°	APR. Alex	TITLE: 0.5 Pitch D型单槽制BTB公座胶芯(料号3.3)			
.XX±0.2	.X.* ±	CHK. Jack	DWG NO. XY-DF533D-NCJGDW			
.XXX±0.1	.XX.* ±	DRA. Can	PROJ. 		CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A