


技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 1000\text{M}\Omega$ 。



序号	品名	材质
①	0.8 Pitch F型 单排立式BTB插座芯	PA9T UL94 V-0, 颜色: 黑色
②	0.8 Pitch F型 单排立式插座端子	铜合金/表面镀金
③	0.8 Pitch B型 单排立式BTB芯柱	耐高温不干胶
总高(H)		公差带高(H1)
4.00		2.80
4.50		3.30
5.00		3.80
5.50		4.30
6.00		4.80
6.50		5.30
7.00		5.80
		公差带高(H2)
		2.90
		3.40
		3.90

Part No	CKT	A	B	C	D
XY-DF829F-6LBMDW	2*3	4.30	2.80	1.60	3.40
XY-DF829F-8LBMDW	2*4	5.10	3.60	2.40	4.20
XY-DF829F-10LBMDW	2*5	5.90	4.40	3.20	5.00
XY-DF829F-12LBMDW	2*6	6.70	5.20	4.00	5.80
XY-DF829F-14LBMDW	2*7	7.50	6.00	4.80	6.60
XY-DF829F-16LBMDW	2*8	8.30	6.80	5.60	7.40
XY-DF829F-18LBMDW	2*9	9.10	7.60	6.40	8.20
XY-DF829F-20LBMDW	2*10	9.90	8.40	7.20	9.00
XY-DF829F-30LBMDW	2*15	13.90	12.40	11.20	13.00
XY-DF829F-40LBMDW	2*20	17.90	16.40	15.20	17.00
XY-DF829F-50LBMDW	2*25	21.90	20.40	19.20	21.00
XY-DF829F-60LBMDW	2*30	25.90	24.40	23.20	25.00
XY-DF829F-70LBMDW	2*35	29.90	28.40	27.20	29.00
XY-DF829F-80LBMDW	2*40	33.90	32.40	31.20	33.00
XY-DF829F-90LBMDW	2*45	37.90	36.40	35.20	37.00
XY-DF829F-100LBMDW	2*50	41.90	40.40	39.20	41.00

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X $\pm$ 0.5	X.* $\pm$ 1°	APR.	Alex	TITLE: 0.8 Pitch F型单排立式BTB插座芯(单#2.9)	
.XX $\pm$ 0.2	.X* $\pm$	CHK.	Jack	DWG NO. XY-DF829F-NLBMDW	
.XXX $\pm$ 0.1	.XX* $\pm$	DRA.	Can	PROJ. CUSTOMER DRAWING	
		SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A