







Part No	CKT	A	B
XY-HY2.0-2A11-BL	2	2.0	6.0
XY-HY2.0-3A11-BL	3	4.0	8.0
XY-HY2.0-4A11-BL	4	6.0	10.0
XY-HY2.0-5A11-BL	5	8.0	12.0
XY-HY2.0-6A11-BL	6	10.0	14.0
XY-HY2.0-7A11-BL	7	12.0	16.0
XY-HY2.0-8A11-BL	8	14.0	18.0
XY-HY2.0-9A11-BL	9	16.0	20.0
XY-HY2.0-10A11-BL	10	18.0	22.0
XY-HY2.0-11A11-BL	11	20.0	24.0
XY-HY2.0-12A11-BL	12	22.0	26.0
XY-HY2.0-13A11-BL	13	24.0	28.0
XY-HY2.0-14A11-BL	14	26.0	30.0
XY-HY2.0-15A11-BL	15	28.0	32.0
XY-HY2.0-16A11-BL	16	30.0	34.0
XY-HY2.0-17A11-BL	17	32.0	36.0
XY-HY2.0-18A11-BL	18	34.0	38.0
XY-HY2.0-19A11-BL	19	36.0	40.0
XY-HY2.0-20A11-BL	20	38.0	42.0


序号	品名	材质
①	HY2.0直针WTB嵌芯	LCP UL94V-0 本色
②	HY2.0直针WTB端子	铜合金/表面镀锡
③	2.00 F型立式2代WTB吸盖	LCP UL94V-0 本色

技术指标(Technical Index):

- 温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 额定电压(Rated voltage):200V,AC.
- 额定电流(Rated current):2.0A AC,DC.
- 接触电阻(Contact resistance): $\leq 25\text{m}\Omega$.
- 耐压值(Withstanding voltage):500V AC/minute.
- 绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.




DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*± 5°	APR.	Alex	TITLE: HY2.0直针WTB	
.XX±0.25	.X.*± 3°	CHK.	Jack	DWG NO. XY-HY2.0-NA11-BL	
.XXX±0.15	.XX.*± 1°	DRA.	Can	PROJ. 	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1



NOTE(注):

- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
(10片孔距累积公差 $\pm 0.2\text{mm}$.)
- 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
(载带拱/浪形MAX:1/100mm.)
- 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
(所有尺寸要满足协会EIA-481规范.)
- 4.MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING.
(载带材料: 透明防静电 PS, 冲封.)
- 5.THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.50 \pm 0.05\text{mm}$.)
- 6.PACKING LENGTH PER REEL: 5.28 METERS. (每卷包装长度: 5.28米.)
- 7.COMPONENT LOAD PER REEL: 400 PCS. (每卷包装数量: 400只.)
8. 纸带装前以不超过装带线为准, 空余位置用塑料泡沫及限位龙填充.
9. 纸带分小、中、标准型3种规格型号: 装带为整箱(在下包装量)采用标准型纸带包装, 未达到整箱数量以产品适当采用小型或中型纸带包装.



纸带型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Height (CM)	7.5	15	32

CKT (2.0mm pitch)	B0	W	F	S
2	6.30	24	11.50	
3	8.30			
4	10.30			
5	12.30			
6	14.30	32	14.20±0.10	28.4
7	16.30			
8	18.30			
9	20.30			
10	22.30	44	20.20±0.10	40.40
11	24.30			
12	26.30			
13	28.30			
14	30.30	56	26.2±0.10	52.40
15	32.30			
16	34.30			
17	36.30			
18	38.30			
19	40.30			
20	42.30			

CKT (2.0mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	24	400	14	5600
3		400	10	4000
4				
5				
6	32	400	8	3200
7				
8				
9				
10	44	400	6	2400
11				
12				
13				
14	56	400	5	2000
15				
16				
17				
18				
19				
20				

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.35	X.*± 5°	APR.	Alex	TITLE: HY2.0直插WTB载带封装		
.XX±0.25	.X.*± 3°	CHK.	Jack	DWG NO. XY-HY2.0-NA11-BL		
.XXX±0.15	.XX.*± 1°	DRA.	Can	PROJ. 		CUSTOMER DRAWING
				SIZE A4	SCALE 1:1	SHEET 1/1