

| REV. | Q'TY | ECN. NO. | APR. | DATE |
|------|------|----------|------|------|
|      |      |          |      |      |






| 序号 | 品名                        | 材质                     |
|----|---------------------------|------------------------|
| ①  | 0.8 Pitch B型立式<br>BTB等座端芯 | LCP UL94 V-0,<br>颜色:本色 |
| ②  | 0.8 Pitch B型立式<br>BTB等座端子 | 铜合金/表面镀金               |
| ③  | 0.8 Pitch B型立式<br>BTB等座底座 | 不锈钢                    |

| Part No            | CKT   | A     | B     | C     |
|--------------------|-------|-------|-------|-------|
| XY-DF837B-20LBMDW  | 2*10  | 7.20  | 13.80 | 12.20 |
| XY-DF837B-22LBMDW  | 2*11  | 8.00  | 14.60 | 13.00 |
| XY-DF837B-24LBMDW  | 2*12  | 8.80  | 15.40 | 13.80 |
| XY-DF837B-26LBMDW  | 2*13  | 9.60  | 16.20 | 14.60 |
| XY-DF837B-28LBMDW  | 2*14  | 10.40 | 17.00 | 15.40 |
| XY-DF837B-30LBMDW  | 2*15  | 11.20 | 17.80 | 16.20 |
| XY-DF837B-32LBMDW  | 2*16  | 12.00 | 18.60 | 17.00 |
| XY-DF837B-34LBMDW  | 2*17  | 12.80 | 19.40 | 17.80 |
| XY-DF837B-36LBMDW  | 2*18  | 13.60 | 20.20 | 18.60 |
| XY-DF837B-38LBMDW  | 2*19  | 14.40 | 21.00 | 19.40 |
| XY-DF837B-40LBMDW  | 2*20  | 15.20 | 21.80 | 20.20 |
| XY-DF837B-42LBMDW  | 2*21  | 16.00 | 22.60 | 21.00 |
| XY-DF837B-44LBMDW  | 2*22  | 16.80 | 23.40 | 21.80 |
| XY-DF837B-46LBMDW  | 2*23  | 17.60 | 24.20 | 22.60 |
| XY-DF837B-48LBMDW  | 2*24  | 18.40 | 25.00 | 23.40 |
| XY-DF837B-50LBMDW  | 2*25  | 19.20 | 25.80 | 24.20 |
| .....              | ...   | ...   | ...   | ...   |
| XY-DF837B-200LBMDW | 2*100 | 79.20 | 85.80 | 84.20 |


| DIMENSION IN mm                      |        | 厦门市辛译精密电子有限公司<br>Xiamen XinYi Xyconn Electronics Co.,Ltd |      |                                                                                                              |           |
|--------------------------------------|--------|----------------------------------------------------------|------|--------------------------------------------------------------------------------------------------------------|-----------|
| TOLERANCE UNLESS OTHERWISE SPECIFIED |        | TITLE: 0.8 Pitch B型立式BTB等座端芯(料3.7)                       |      |                                                                                                              |           |
| .X±0.5                               | X.*±1° | APR.                                                     | Alex | DWG NO. XY-DF837B-NLBMDW                                                                                     |           |
| .XX±0.2                              | .X.*±  | CHK.                                                     | Jack | PROJ.  CUSTOMER DRAWING |           |
| .XXX±0.1                             | .XX.*± | DRA.                                                     | Can  | SIZE A4                                                                                                      | SCALE 1:1 |
|                                      |        | SHEET 1/1                                                |      | REV.                                                                                                         | A         |

## 技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 100V. AC.
4. 接触电阻: <0.05Ω.
5. 绝缘电阻: >500MΩ



适用线路板



DIMENSION IN mm

TOLERANCE UNLESS  
OTHERWISE SPECIFIED

.X±0.5

X.\*±1°

APR.

Alex

.XX±0.2

.X\*±

CHK.

Jack

.XXX±0.1

.XX\*±

DRA.

Can

厦门市辛译精密电子有限公司  
Xiamen XinYi Xyeconn Electronics Co.,Ltd

TITLE: 0.8 Pitch BMTB母座(精3.7)

DWG NO. XY-DF837B-NLBMDW

PROJ.

CUSTOMER DRAWING

SIZE A4

SCALE 1:1

SHEET 1/1

REV. A