







技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

合高(H)

公座单高

母座单高

序号

品名

材质

3.0

2.2

2.2

①

0.5 Pitch B型单槽立

LCP

3.5

2.2

2.7

②

0.5 Pitch B型单槽立

UL94 V-0 颜色: 米黄色

4.0

2.2

3.2

式BTB等座端子

铜合金/表面镀金

5.0

2.6

4.4

Part No	CKT	A	B	C	D
XY-DF544B-10LBMDW	2X5	2.00	3.20	4.70	4.10
XY-DF544B-12LBMDW	2X6	2.50	3.70	5.20	4.60
XY-DF544B-14LBMDW	2X7	3.00	4.20	5.70	5.10
XY-DF544B-16LBMDW	2X8	3.50	4.70	6.20	5.60
XY-DF544B-18LBMDW	2X9	4.00	5.20	6.70	6.10
XY-DF544B-20LBMDW	2X10	4.50	5.70	7.20	6.60
XY-DF544B-22LBMDW	2X11	5.00	6.20	7.70	7.10
XY-DF544B-24LBMDW	2X12	5.50	6.70	8.20	7.60
XY-DF544B-26LBMDW	2X13	6.00	7.20	8.70	8.10
XY-DF544B-28LBMDW	2X14	6.50	7.70	9.20	8.60
XY-DF544B-30LBMDW	2X15	7.00	8.20	9.70	9.10
XY-DF544B-32LBMDW	2X16	7.50	8.70	10.20	9.60
XY-DF544B-34LBMDW	2X17	8.00	9.20	10.70	10.10
XY-DF544B-36LBMDW	2X18	8.50	9.70	11.20	10.60
XY-DF544B-38LBMDW	2X19	9.00	10.20	11.70	11.10
XY-DF544B-40LBMDW	2X20	9.50	10.70	12.20	11.60
XY-DF544B-44LBMDW	2X22	10.50	11.70	13.20	12.60
XY-DF544B-50LBMDW	2X25	12.00	13.20	14.70	14.10
XY-DF544B-60LBMDW	2X30	14.50	15.70	17.20	16.60
XY-DF544B-70LBMDW	2X35	17.00	18.20	19.70	19.10
XY-DF544B-80LBMDW	2X40	19.50	20.70	22.20	21.60

DIMENSION IN mm

TOLERANCE UNLESS
OTHERWISE SPECIFIED

.X±0.5

X.*±1°

APR.

Alex

TITLE:

Pitch B型单槽立式BTB等座端子(单高4.4)无刷片镀金

.XX±0.2

.X.*±

CHK.

Jack

DWG NO.

XY-DF544B-NLBMDW

.XXX±0.1

.XX.*±

DRA.

Can

PROJ.

SCALE 1:1

SHEET

1/1

REV.

A

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd