






技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 50V. AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100M\Omega$




High photosynthesis 高(H)	The female seat neight (H1)	The male seat neight (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

序号	品名	材质	DIMENSION IN mm	
			TOLERANCE UNLESS OTHERWISE SPECIFIED	
①	0.5 Pitch双端立式BTB等座板	PA10T UL94 V-0 颜色:黑色	.X±0.5	X.*±1°
②	0.5 Pitch双端立式BTB等座端子	铜合金/表面点镀金	.XX±0.2	.X°±
③	0.5 Pitch双端立式BTB等座簧	LCP UL94 V-0颜色:黑色.	.XXX±0.1	.XX°±

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd

APR.	Alex	TITLE: 0.5 Pitch双端立式BTB等(料3.5)	
CHK.	Jack	DWG NO. XY-DF535A-NLBMDW	
DRA.	Can	CUSTOMER DRAWING	
SIZE	A4	SCALE	1:1
SHEET	1/1	REV.	A



WWW.XYECOMM.COM

REV.	Q'TY	ECN. NO.	APR.	DATE

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*± 1°	APR. Alex	TITLE: 0.5 Pitch 1.27mm BTB#(3.5)		
.XX±0.2	.X*±	CHK. Jack	DWG NO. XY-DF535A-NLBMDW		
.XXX±0.1	.XX*±	DRA. Can	PROJ.		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1