





技术指标(Technical Index):








- 1.温度范围(Temperature range): $-40^{\circ}\text{C}\sim+125^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V,AC.
- 3.额定电流(Rated current):3.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Withstanding voltage):1000V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*± 5°	APR. Alex	TITLE: HA2.5##WTB		
.XX±0.25	.X*± 3°	CHK. Jack	DWG NO. XY-XHB2.54-NA21-BL		
.XXX±0.15	.XX*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/1
			REV. A		

NOTE(注):

- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
(10片孔距累积公差 $\pm 0.2\text{mm}$.)
- 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
(载带拱/弯曲MAX:1/100mm.)
- 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
(所有尺寸要满足协会EIA-481规范.)
- 4.MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING.
(载带材料: 透明防静电 PS, 冷封.)
- 5.THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.50 \pm 0.05\text{mm}$.)
- 6.PACKING LENGTH PER REEL: 6.43 METERS. (每卷包装长度: 6.43米.)
- 7.COMPONENT LOAD PER REEL: 500 PCS. (每卷包装数量: 500片.)
8. 纸带包装以不超过载带线为准, 空余位置用塑料泡沫及保尼龙填充.
9. 纸带分小、中、标准型3种规格型号: 载带为整卷(左下包装)采用标准型纸带包装, 未达到整卷数量以产品适当采用小型或中型纸带包装.



标准型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Height (CM)	7.5	15	32

CKT (2.5mm pitch)	B0	W	F	S
2	7.80	24	11.50 ± 0.10	
3	10.30			
4	12.80			
5	15.30			
6	17.80	32	14.20 ± 0.10	28.40
7	20.30			
8	22.80			
9	25.30			
10	27.80	44	20.20 ± 0.10	40.40
11	30.30			
12	32.80			
13	35.30			
14	37.80	56	26.2 ± 0.10	52.40
15	40.30			
16	42.80			

CKT (2.5mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	24	500	10	5000
3				
4				
5				
6	32	500	8	4000
7				
8				
9				
10	44	500	6	3000
11				
12				
13				
14	56	500	5	2500
15				
16				

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.5	X.*± 5°	APR.	Alex	TITLE: XHB2.5##WTB			
.XX±0.25	.X.*± 3°	CHK.	Jack	DWG NO. XY-XHB2.54-NA21-BL			
.XXX±0.15	.XX*± 1°	DRA.	Can	PROJ. 		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A