




A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	



型号	CKT	A	B
WF-0B420A02P	2*1	0.00	5.40
WF-0B420A04P	2*2	4.20	9.60
WF-0B420A06P	2*3	8.40	13.80
WF-0B420A08P	2*4	12.60	18.00
WF-0B420A10P	2*5	16.80	22.20
WF-0B420A12P	2*6	21.00	26.40
WF-0B420A14P	2*7	25.20	30.60
WF-0B420A16P	2*8	29.40	34.80
WF-0B420A18P	2*9	33.40	39.00
WF-0B420A20P	2*10	37.80	43.20
WF-0B420A22P	2*11	42.00	47.40
WF-0B420A24P	2*12	46.20	51.60

技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐压: 1500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 5A AC, DC.



5

序号	品名	材质	GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD						BXCONN [®] 
1	WTB4.2双排弯针胶芯	PA66 UL94V-2 白色	DIM.	TOL.	TITLE: WTB4.2MM WAFER DIP TYPE						
			.x .xx .xxx	±0.30 ±0.25 ±0.15							
2	WTB4.2双排弯针短端子	铜合金/表面镀锡	GENERAL ANGLE:		DWG. NO.: WF-0B420AXP			CHECKED: MAX			
			x. x.x x.x	±5° ±1°							
3	WTB4.2双排弯针长端子	铜合金/表面镀锡			PART NO.: WF-0B420AXP		DRAWN: ELLA				
					UNIT: mm	SCALE: none	SHEET: 1 of 2	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	

