

A	B	C	D	E
REV.		DESCRIPTION	ECN NO.	NAME
				DATE

型号	CKT	A	B
WF-0A420A02P	2*1	0.00	5.40
WF-0A420A04P	2*2	4.20	9.60
WF-0A420A06P	2*3	8.40	13.80
WF-0A420A08P	2*4	12.60	18.00
WF-0A420A10P	2*5	16.80	22.20
WF-0A420A12P	2*6	21.00	26.40
WF-0A420A14P	2*7	25.20	30.60
WF-0A420A16P	2*8	29.40	34.80
WF-0A420A18P	2*9	33.40	39.00
WF-0A420A20P	2*10	37.80	43.20
WF-0A420A22P	2*11	42.00	47.40
WF-0A420A24P	2*12	46.20	51.60

Technical drawing showing dimensions and views:

- Top view: DIM A ± 0.25, 4.20 ± 0.2, DIM B ± 0.30, 9.65 ± 0.3, 4.20
- Side view: 12.90 ± 0.2, 3.55 ± 0.25, 10.15
- Section A-A: SCALE 1:1, N - □ 1.14 ± 0.1, (9.00)
- Bottom view: 10.15

技术指标:

- 温度范围:-25°C~85°C.
- 额定电压:250V AC,DC.
- 耐压:1500V AC/minute.
- 接触电阻:≤20mΩ .
- 绝缘电阻:≥1000MΩ.
- 额定电流: 5A AC,DC.

PCB.WELDING DRAWING (TOLERANCE:±0.05)

序号	品名	材质
1	WTB4.2双排直针胶芯	PA66 UL94V-2 白色
2	WTB4.2双排直针端子	铜合金 /表面镀锡

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM.	TOL.	TITLE: WTB4.2MM WAFER DIP TYPE			
.x	+0.30 ±0.25	DWG. NO.: WF-0A420AXP	CHECKED: MAX		
.xx	+0.15 ±0.10	PART NO.: WF-0A420AXP	DRAWN: ELLA		
.xxx	+0.10 ±0.05	UNIT: mm	SCALE: none	SHEET: 1of 2	DWG. SIZE: A4
GENERAL ANGLE:	±5° ±1°	LAYER: bxconn	APPROVED: WILL		

BXCONN® QR CODE

