




技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 50V, AC.
4. 接触电阻: ≤0.02Ω.
5. 绝缘电阻: ≥100MΩ



High photosynthesis 高(H)	The female seat height (H1)	The male seat height (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

			DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
序号	品名	材质	TOLERANCE UNLESS OTHERWISE SPECIFIED						
①	0.5 Pitch双槽立式BTBA公座板	PA10T UL94 V-0 颜色:黑色	.X±0.5	X.*±1°	APR. Alex	TITLE: 0.5 Pitch双槽立式BTBA(4.0)			
②	0.5 Pitch双槽立式BTBA公座端子	铜合金/表面点镀金	.XX±0.2	.X°±	CHK. Jack	DWG NO. XY-DF540A-NLBGDW			
③	0.5 Pitch双槽立式BTBA公座簧盖	LCP UL94 V-0颜色:黑色.	.XXX±0.1	.XX°±	DRA. Can	PROJ. 		CUSTOMER DRAWING	
						SIZE A4	SCALE 1:1	SHEET 1/1	REV. A

适用线路板



WWW.XYECOMM.COM

REV.	Q'TY	ECN. NO.	APR.	DATE

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
XY-DF540A-8LBDGW	8	1.50	2.50	4.70	3.40	4.00
XY-DF540A-10LBDGW	10	2.00	3.00	5.20	3.90	
XY-DF540A-12LBDGW	12	2.50	3.50	5.70	4.40	
XY-DF540A-14LBDGW	14	3.00	4.00	6.20	4.90	
XY-DF540A-16LBDGW	16	3.50	4.50	6.70	5.40	
XY-DF540A-18LBDGW	18	4.00	5.00	7.20	5.90	
XY-DF540A-20LBDGW	20	4.50	5.50	7.70	6.40	
XY-DF540A-22LBDGW	22	5.00	6.00	8.20	6.90	
XY-DF540A-24LBDGW	24	5.50	6.50	8.70	7.40	
XY-DF540A-26LBDGW	26	6.00	7.00	9.20	7.90	
XY-DF540A-28LBDGW	28	6.50	7.50	9.70	8.40	8.00
XY-DF540A-30LBDGW	30	7.00	8.00	10.20	8.90	
XY-DF540A-32LBDGW	32	7.50	8.50	10.70	9.40	
XY-DF540A-34LBDGW	34	8.00	9.00	11.20	9.90	
XY-DF540A-36LBDGW	36	8.50	9.50	11.70	10.40	
XY-DF540A-38LBDGW	38	9.00	10.00	12.20	10.90	
XY-DF540A-40LBDGW	40	9.50	10.50	12.70	11.40	
XY-DF540A-44LBDGW	44	10.50	11.50	13.70	12.40	
XY-DF540A-50LBDGW	50	12.00	13.00	15.20	13.90	
XY-DF540A-60LBDGW	60	14.50	15.50	17.70	16.40	
XY-DF540A-70LBDGW	70	17.00	18.00	20.20	18.90	
XY-DF540A-80LBDGW	80	19.50	20.50	22.70	21.40	
XY-DF540A-100LBDGW	100	24.50	25.50	27.70	26.40	

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X:± 1°	APR. Alex	TITLE: 0.5 Pitch 1.27mm BTB4 (4.0)		
.XX±0.2	.X°±	CHK. Jack	DWG NO. XY-DF540A-NLBGDW		
.XXX±0.1	.XX°±	DRA. Can	PROJ.		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1