






REV.	Q'TY	ECN. NO.	APR.	DATE




0.1



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

序号	品名	材质
①	0.5 Pitch B型单插式BTB公座贴片	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型单插式BTB公座端子	铜合金/表面镀金
③	0.5 Pitch B型单插式BTB公座焊片	铜合金/表面镀锡

Part No	CKT	A	B	C	D	E
XY-DF526B-10LBGDH	2X5	2.00	3.10	4.60	5.52	4.10
XY-DF526B-12LBGDH	2X6	2.50	3.60	5.10	6.02	4.60
XY-DF526B-14LBGDH	2X7	3.00	4.10	5.60	6.52	5.10
XY-DF526B-16LBGDH	2X8	3.50	4.60	6.10	7.02	5.60
XY-DF526B-18LBGDH	2X9	4.00	5.10	6.60	7.52	6.10
XY-DF526B-20LBGDH	2X10	4.50	5.60	7.10	8.02	6.60
XY-DF526B-22LBGDH	2X11	5.00	6.10	7.60	8.52	7.10
XY-DF526B-24LBGDH	2X12	5.50	6.60	8.10	9.02	7.60
XY-DF526B-26LBGDH	2X13	6.00	7.10	8.60	9.52	8.10
XY-DF526B-28LBGDH	2X14	6.50	7.60	9.10	10.02	8.60
XY-DF526B-30LBGDH	2X15	7.00	8.10	9.60	10.52	9.10
XY-DF526B-32LBGDH	2X16	7.50	8.60	10.10	11.02	9.60
XY-DF526B-34LBGDH	2X17	8.00	9.10	10.60	11.52	10.10
XY-DF526B-36LBGDH	2X18	8.50	9.60	11.10	12.02	10.60
XY-DF526B-38LBGDH	2X19	9.00	10.10	11.60	12.52	11.10
XY-DF526B-40LBGDH	2X20	9.50	10.60	12.10	13.02	11.60
XY-DF526B-44LBGDH	2X22	10.50	11.60	13.10	14.02	12.60
XY-DF526B-50LBGDH	2X25	12.00	13.10	14.60	15.52	14.10
XY-DF526B-60LBGDH	2X30	14.50	15.60	17.10	18.02	16.60
XY-DF526B-70LBGDH	2X35	17.00	18.10	19.60	20.52	19.10
XY-DF526B-80LBGDH	2X40	19.50	20.60	22.10	23.02	21.60

DIMENSION IN mm		TOLERANCE UNLESS OTHERWISE SPECIFIED			
.X±0.5	X.*±1°	APR.	Alex	TITLE: 0.5 Pitch B型单插式BTB公座贴片(料2.6)	
.XX±0.2	.X.*±	CHK.	Jack	DWG NO. XY-DF526B-NLBGDH	
.XXX±0.1	.XX.*±	DRA.	Can	PROJ. CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A	F-RD-18A	