




REV.	Q'TY	ECN. NO.	APR.	DATE

序号	品名	材质
①	0.8 Pitch B型立式 BTB公座胶芯	LCP UL94 V-0, 颜色:本色
②	0.8 Pitch B型立式 BTB公座端子	铜合金/表面镀金
③	0.8 Pitch B型立式 BTB公座壳体	不锈钢




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 100V, AC。
4. 接触电阻: $\leq 0.05\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$

Part No	CKT	A	B	C
XY-DF877B-20LBGDW	2*10	7.20	13.80	12.20
XY-DF877B-22LBGDW	2*11	8.00	14.60	13.00
XY-DF877B-24LBGDW	2*12	8.80	15.40	13.80
XY-DF877B-26LBGDW	2*13	9.60	16.20	14.60
XY-DF877B-28LBGDW	2*14	10.40	17.00	15.40
XY-DF877B-30LBGDW	2*15	11.20	17.80	16.20
XY-DF877B-32LBGDW	2*16	12.00	18.60	17.00
XY-DF877B-34LBGDW	2*17	12.80	19.40	17.80
XY-DF877B-36LBGDW	2*18	13.60	20.20	18.60
XY-DF877B-38LBGDW	2*19	14.40	21.00	19.40
XY-DF877B-40LBGDW	2*20	15.20	21.80	20.20
XY-DF877B-42LBGDW	2*21	16.00	22.60	21.00
XY-DF877B-44LBGDW	2*22	16.80	23.40	21.80
XY-DF877B-46LBGDW	2*23	17.60	24.20	22.60
XY-DF877B-48LBGDW	2*24	18.40	25.00	23.40
XY-DF877B-50LBGDW	2*25	19.20	25.80	24.20
.....	...	...	...	...
XY-DF877B-200LBGDW	2*100	79.20	85.80	84.20

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.5	X* ± 1°	APR.	Alex	TITLE: 0.8 Pitch B型立式BTB公座胶芯(料7.7)			
.XX±0.2	.X* ±	CHK.	Jack	DWG NO. XY-DF877B-NLBGDW			
.XXX±0.1	.XX* ±	DRA.	Can	PROJ. 		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*± 1°	APR. Alex	TITLE: 0.8 Pitch 0.8 Pitch 0.8 Pitch (精7.7)		
.XX±0.2	.X.*±	CHK. Jack	DWG NO. XY-DF877B-NLBGDW		
.XXX±0.1	.XX.*±	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/1