





Technical Index:

1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 5A AC, DC.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Dielectric withstanding voltage: 1500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.
7. Apply to gauge: AWG#22~#28 (O.D 1.80mm Max).

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN[®]	
DIM.	TOL.	TITLE: WBM4.2MM TERMINAL						
.x	±0.30							
.xx	±0.25							
.xxx	±0.15							
GENERAL ANGLE:								
x.°	±5°	DWG. NO.: WF-1C420A			CHECKED: MAX			
x.x°	±1°	PART NO.: WF-1C420A			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	