



技术指标:


1. 塑料表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 50V, AC.
4. 接触电阻: <0.02Ω.
5. 绝缘电阻: ≥100MΩ

High photosynthesis 高 (H)	The female seat height (H1)	The male seat height (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90



序号	品名	材质
①	0.5 Pitch 双端式 BTB 公座端子	PA10T UL94 V-0 颜色: 黑色
②	0.5 Pitch 双端式 BTB 公座端子	铜合金/表面镀金
③	0.5 Pitch 双端式 BTB 公座端子	LCP UL94 V-0 颜色: 黑色

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*±1°	APR.	Alex	TITLE: 0.5 Pitch 双端式 BTB (间距 2.0)	
.XX±0.2	.X.*±	CHK.	Jack	DWG NO. XY-DF520A-NLBGDW	
.XXX±0.1	.XX.*±	DRA.	Can	PROJ. CUSTOMER DRAWING	
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A



WWW.XYECOMM.COM

REV.	Q'TY	ECN. NO.	APR.	DATE

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*± 1°	APR. Alex	TITLE: 0.5 Pitch 1.27mm BTB4 (2.0)		
.XX±0.2	.X*±	CHK. Jack	DWG NO. XY-DF520A-NLBGDW		
.XXX±0.1	.XX*±	DRA. Can	PROJ.		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1 REV. A