







REV.	Q'TY	ECN. NO.	APR.	DATE

序号	品名	材质
①	0.5 Pitch B型单槽立式BTB等座端子	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型单槽立式BTB等座端子	铜合金/表面镀锡/表面点镀金



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 125V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100M\Omega$

合高(H)	公座单高	母座单高	Part No	CKT	A	B	C	D
3.0	2.2	2.2	XY-DF522B-10LBMDW	2X5	2.00	3.20	4.70	4.10
3.5	2.2	2.7	XY-DF522B-12LBMDW	2X6	2.50	3.70	5.20	4.60
4.0	2.2	3.2	XY-DF522B-14LBMDW	2X7	3.00	4.20	5.70	5.10
5.0	2.6	4.4	XY-DF522B-16LBMDW	2X8	3.50	4.70	6.20	5.60
			XY-DF522B-18LBMDW	2X9	4.00	5.20	6.70	6.10
			XY-DF522B-20LBMDW	2X10	4.50	5.70	7.20	6.60
			XY-DF522B-22LBMDW	2X11	5.00	6.20	7.70	7.10
			XY-DF522B-24LBMDW	2X12	5.50	6.70	8.20	7.60
			XY-DF522B-26LBMDW	2X13	6.00	7.20	8.70	8.10
			XY-DF522B-28LBMDW	2X14	6.50	7.70	9.20	8.60
			XY-DF522B-30LBMDW	2X15	7.00	8.20	9.70	9.10
			XY-DF522B-32LBMDW	2X16	7.50	8.70	10.20	9.60
			XY-DF522B-34LBMDW	2X17	8.00	9.20	10.70	10.10
			XY-DF522B-36LBMDW	2X18	8.50	9.70	11.20	10.60
			XY-DF522B-38LBMDW	2X19	9.00	10.20	11.70	11.10
			XY-DF522B-40LBMDW	2X20	9.50	10.70	12.20	11.60
			XY-DF522B-44LBMDW	2X22	10.50	11.70	13.20	12.60
			XY-DF522B-50LBMDW	2X25	12.00	13.20	14.70	14.10
			XY-DF522B-60LBMDW	2X30	14.50	15.70	17.20	16.60
			XY-DF522B-70LBMDW	2X35	17.00	18.20	19.70	19.10
			XY-DF522B-80LBMDW	2X40	19.50	20.70	22.20	21.60

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: 0.5 Pitch B型单槽立式BTB等座端子(料号2.2)无刷片点镀金			
.X±0.5	X.*±1°	APR.	Alex	DWG NO. XY-DF522B-NLBMDW	
.XX±0.2	.X.*±	CHK.	Jack	PROJ. CUSTOMER DRAWING	
.XXX±0.1	.XX.*±	DRA.	Can	SIZE A4	SCALE 1:1
		SHEET 1/1		REV. A	