

SPECIFICATION:

1.MATERIAL:

HOUSING: LCP UL 94V-0

COLOR: BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:


CONTACT:1u"3u"5u"15u" GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDER TAILS







30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL



ITEM	DIM A	形状	DIM B
SATA-08M-22BWB-C21	2.10		2.08
SATA-08M-22BWB-C23	2.30		

RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE:±0.05

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE:SATA 7+15P 母座SMT H:3.50 板上侧插式		
DECIMALS:		PAR	SATA-08M-22BWB-CN	
ANGLES:		DWN	Lucas	
.X':±0.30		CHKD	Ethan	
.XX':±0.20		APVD	Jacob	
.XXX':±0.05		SCALE:1:1	UNIT:MM	
CUSTOMER COPY		SIZE:A4	SHEET:1F1	REV:A