




Part No	CKT	A	B	C
WAFER-PE1.2-2PJK-GB	2	3.10	1.20	2.60
WAFER-PE1.2-3PJK-GB	3	4.30	2.40	3.80
WAFER-PE1.2-4PJK-GB	4	5.50	3.60	5.00
WAFER-PE1.2-5PJK-GB	5	6.70	4.80	6.20
WAFER-PE1.2-6PJK-GB	6	7.90	6.00	7.40
WAFER-PE1.2-7PJK-GB	7	9.10	7.20	8.60
WAFER-PE1.2-8PJK-GB	8	10.30	8.40	9.80
WAFER-PE1.2-9PJK-GB	9	11.50	9.60	11.00
WAFER-PE1.2-10PJK-GB	10	12.70	10.80	12.20
WAFER-PE1.2-11PJK-GB	11	13.90	12.00	13.40
WAFER-PE1.2-12PJK-GB	12	15.10	13.20	14.60

技术指标:

- 1.温度范围: -25°C~85°C.
- 2.额定电压: 50V AC,DC.
- 3.耐电压: 500V AC/minute.
- 4.接触电阻: $\leq 20\text{m}\Omega$.
- 5.绝缘电阻: $\geq 100\text{M}\Omega$.
- 6.额定电流: 1.5A AC,DC.

材质:

- 1.塑胶: LCP, 黑色

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 1.2Pitch B型电池座公头胶壳		
			PAR	WAFER-PE1.2-NPJUK-GB	
DECIMALS:	ANGLES:		DWN	Lucas	
X.:±0.50	±1°		CHKD	Ethan	
X.X:±0.20			APVD	Jacob	
X.XX:±0.10			SCALE1:1	UNIT:MM	
		CUSTOMER COPY	SIZE:A4	SHEET:1F1	REV:A