





SPECIFICATIONS

RATED VALUE: 125V AC 1.5 Amps
Insulation Resistance:1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 500V
Operation Temperature:-40° to+105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240° C for30-60seconds
(260° C for 5 seconds)



RECOMMEND P. C. B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)



深圳市韩下电子有限公司

UNLESS OTHEWIXE SPECIFIED TOLERANCE

X :±0.30 X° :±5°
X.X :±0.25 X.X° :±1°
X.XX:±0.20 X.XX° :±0.5°

DRAWM NAME:

HX PM2.0-2x5P TP H4.3

SIZE

A4

SCALE

N:1

PROUCT NO.

REV

A

UNIT

mm

PROJECT

⌀

⌀

PAGE

1/1

DRAWN :

黄彬

2023/03/23

CHECKED:

张伟

/

/

APPROVED:

罗小春

/

/

No. of

DIM. A

DIM. B

No. of

DIM. A

DIM. B

No. of

DIM. A

DIM. B

No. of

DIM. A

DIM. B

1

0.00

2.00

11

20.00

22.00

21

40.00

42.00

31

60.00

62.00

2

2.00

4.00

12

22.00

24.00

22

42.00

44.00

32

62.00

64.00

3

4.00

6.00

13

24.00

26.00

23

44.00

46.00

33

64.00

66.00

4

6.00

8.00

14

26.00

28.00

24

46.00

48.00

34

66.00

68.00

5

8.00

10.00

15

28.00

30.00

25

48.00

50.00

35

68.00

70.00

6

10.00

12.00

16

30.00

32.00

26

50.00

52.00

36

70.00

72.00

7

12.00

14.00

17

32.00

34.00

27

52.00

54.00

37

72.00

74.00

8

14.00

16.00

18

34.00

36.00

28

54.00

56.00

38

74.00

76.00

9

16.00

18.00

19

36.00

38.00

29

56.00

58.00

39

76.00

78.00

10

18.00

20.00

20

38.00

40.00

30

58.00

60.00

40

78.00

80.00



深圳市韩下电子有限公司
Shenzhen Hanxia Electronic Co.,Ltd
Tel:0755-23086569

承 认 书

SPECIFICATION FOR APPROVAL

产 品 编 码
Material code:

产品名称 Project:

排母

规格型号 Part No:

HX PM2.0-2x5P TP H4.3

贵公司承认印 Approval signatures

料 号/Part No.	签 章/Signatures

日期 Date:

拟制/Drawn	黄彬	
审核/Check	张伟	
批准/Approved	罗小春	