


SPECIFICATION

Physical Dimensions(尺寸图):

Unit( 单位):mm



| Item(项目) | Dimension(尺寸) | Tolerance(公差范围) | Unit(单位) |
|----------|---------------|-----------------|----------|
| A        | 13.0          | ±0.5            | mm       |
| B        | 6.5           | ±0.5            | mm       |
| C        | 8.0           | ±0.5            | mm       |
|          |               |                 |          |
|          |               |                 |          |

Electrical requirements(电气特性):

Z1=15 Ω Min at 25 MHz ;Z2=40 Ω Min at 100 MHz

Electrical requirements(电气特性):

Testing Equipment(测试仪器):E4991A + 16194A

Test frequency range(测试频率区间):1-500MHz

Test lead set(测试线组):Ø0.5x0.5TSx100L(mm)

| Model.(型号) | Unit( 单位) | Rev.( 版本) | Dimension Limit( 尺寸范围) | Tolerance( 公差) |
|------------|-----------|-----------|------------------------|----------------|
| V18089T    | mm        | Rev.4.0   | 0 ~ 10                 | ±0.5           |
|            |           |           | 10 ~ 100               | ±1.0           |
|            |           |           | 100 ~ 150              | ±1.5           |
|            |           |           | 150 ~ 250              | ±2.0           |

