





SPECIFICATION:

1.MATERIAL:

HOUSING: LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:




CONTACT:1u" GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL





PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL



RECOMMEND PCB LAYOUT (T=1.2)

PCB TOLERANCE:±0.05



ITEM	DIM A	形状	DIM B
SATA-02M-22AWB-C21	2.10		2.08
SATA-02M-22AWB-C23	2.30		

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:SATA 7+15P 母座 SMT H:6.74 板下型侧插	
			PAR	SATA-02M-22AWB-CN
			DWN	Lucas
			CHKD	Ethan
			APVD	Jacob
DECIMALS:	ANGLES:	SCALE:1:1	UNIT:MM	
.X:±0.30	.X':±3°	SIZE:A4	SHEET:1F1	REV:A
.XX:±0.20	.XX':±2°			
.XXX:±0.05	.XXX':±0.5°	CUSTOMER COPY		