

SPECIFICATION:

1.MATERIAL:

HOUSING:LCP UL 94V-0

COLOR:BLACK

CONTACT:PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG:BRASS C2680R-H,T=0.30mm

2.FINISH:






CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDERTAILS



30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL



环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE:±0.05

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			
DECIMALS:	ANGLES:	TITLE:SATA 7+15P 母座 SMT H:6.74 板上型	
.X:±0.30	.X':±3°	PAR	SATA-14M-22BWB-C23
.XX:±0.20	.XX':±2°	DWN	Lucas
.XXX:±0.05	.XXX':±0.5°	CHKD	Ethan
CUSTOMER COPY		APVD	Jacob
		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A