



SPECIFICATION:

Current Rating	: 1A
Dielectric Withstanding	: AC 500V
Contact Resistance	: 20mΩ Max.
Insulator Resistance	: 1000MΩ
Operating Temperature	: -40℃~+105℃
Max Processing Temp	: 230℃ for 30~60 seconds
Contact Material	: Phosphor Bronze (C5191)
Insulator Material	: Nylon-6T UL94V-0
Contact Plating	: Gold plated



PCB LAYOUT

APPROVED:		DATE:		Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD							
CHECKED:		DATE:		TITLE: 220-1S-1*15P H=4.3mm DIP:2.4mm							
DRAWN:		DATE:		CLIENT P/N B-2201S15P-A120							
LYF		2026-08-18		UNIT mm		SCALE free					
TOLERANCE TABLE				FILE NO.		Ckmtw-220-10007		REV.		A	
.0		±0.20									
.00		±0.10									
.000		±0.05									