

SPECIFICATION:

1.MATERIAL:

HOUSING: LCP UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:






CONTACT:1~15u" GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL

RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE:±0.05

ITEM	DIM A	形状	DIM B
SATA-01M-22AWB-C21	2.10		2.08
SATA-01M-22AWB-C23	2.30		

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE:SATA 7+15P 母座SMT带三粒 H:4.20 板下型侧插鱼叉		
DECIMALS:	ANGLES:	PAR	SATA-01M-22AWB-CN	
.X:±0.30	.X':±3°	DWN	Lucas	
.XX:±0.20	.XX':±2°	CHKD	Ethan	
.XXX:±0.05	.XXX':±0.5°	APVD	Jacob	
CUSTOMER COPY		SCALE:1:1	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A