






PIN 定义:

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	SSTXp1	B11	SSRXp1
A3	SSTXn1	B10	SSRXn1
A4	Vbus	B9	Vbus
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	Vbus	B4	Vbus
A10	SSRXn2	B3	SSTXn2
A11	SSRXp2	B2	SSTXp2
A12	GND	B1	GND



ALL SOLDER-TAIL



NOTES:

SPECIFICATION:

- 1.CURRENT RATING: 5A MAX
- 2.VOLTAGE:100 VAC
- 3.TEMPERATURE RANGE: -40°C~85°C
- 4.CONTACT RESISTANCE: 40 MILLIONHM MAX.
- 5.INSULATION RESISTANCE: 100 MEGOHMS MIN.
- 6.INSERTION FORCE: 5N~20N
- 7.UNMATING FORCE: 8N~20N
- 8.DURABILITY:10,000CYCLES

⑥	CAP	1	LCP, BLACK	/
⑤	BOTTOM CONTACT	24	C7025	NI 50u" Min AND Au 1u" PLATED ON CONTACT POINT NI 50u" Min AND TIN 100u"MIN PLATED ON SOLDER AREA
④	SHELL	1	SUS304	WELDABLE NI 30u"NI PLATED ON SOLDER AREA
③	EMC SHELL	1	SUS316	WATER CLEAN
②	HOUSING	1	LCP, BLACK	/
①	MIDDLE PLATE	1	SUS301	WATER CLEAN
NO.	DESCRIPTION	Q'TY	MATERIAL	THE PLATING
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES				TITLE:Type-C 24Pin REC.Vertical TYPE H=14
DECIMALS:		ANGLES:		PAR
X.:±0.50		X.':±5°		DWN Lucas
X.X:±0.30		X.X':±3°		CHKD Ethan
X.XX:±0.15		X.XX':±1°		APVD Jacob
CUSTOMER COPY		SCALE:1:1		UNIT:MM
		SIZE:A4		SHEET:1F2
				REV:A



1. 10 POCKETS HOLE PITCH CUMULATIVE TOLERANCE $2 \pm 0.20\text{MM}$.
2. NUMBER OF CONNECTORS: 250 PCS/REEL.

MANUFACTURE DWG		 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:Type-C 24Pin	
			REC.Vertical TYPE H=14	
PAR	TYPEC-514L-ACP24-H14			
DWN	Lucas			
CHKD	Ethan			
APVD	Jacob			
SCALE1:1	UNIT:MM			
X.:±0.50	X.:±1°	CUSTOMER COPY		
X.X:±0.30	X.X':±3°			
X.XX:±0.15	X.XX':±1°	SIZE:A4	SHEET:2F2	REV:A