

SPECIFICATION:

1.MATERIAL:

HOUSING: LCP E130i 30% G/F UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.20mm

2.FINISH:




CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

RECOMMENDED PCB LAYOUT
UNLESS TOLERANCE: +/ -0.05

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE:SATA 7+15P 直立式SMT 带接地片	
DECIMALS:	ANGLES:	PAR	SATA-16M-22BLB-H81
.X:±0.30	.X':±3°	DWN	Lucas
.XX:±0.20	.XX':±2°	CHKD	Ethan
.XXX:±0.05	.XXX':±0.5°	APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A