






技术指标(Technical Index):

- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):50V DC/AC(rms).
- 3.额定电流(Rated current):1.5A,AC/DC(AWG#28).
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage):500V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 100\text{M}\Omega$.
- 7.适用线规(Apply to gauge):AWG28#~AWG30#
(O.D 0.5mm-0.7mm).

P/N	材质	镀层
WAFER-PE1.2-DZ-GA	磷青铜	镀金1 μ "
WAFER-PE1.2-DZ-GC		镀锡

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 1.2Pitch B型电池座公头端子	
			PAR	WAFER-PE1.2-DZ-GX
DECIMALS:	ANGLES:		DWN	Lucas
X.:±0.50	±1°		CHKD	Ethan
X.X:±0.20			APVD	Jacob
X.XX:±0.10		CUSTOMER COPY	SCALE:1:1	UNIT:MM
			SIZE:A4	SHEET:1F1
				REV:A