








适用线路板(PCB LAYOUT)



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 50V AC, DC.
4. 耐电压: 500V AC/minute.
5. 接触电阻: $\leq 20\text{m}\Omega$.
6. 绝缘电阻: $\geq 100\text{M}\Omega$.
7. 额定电流: 1.5A AC, DC.

Part No	CKT	A	B	C	D
WAFER-PE1.2-2PWB-B4C	2	4.20	1.20	2.65	3.64
WAFER-PE1.2-3PWB-B4C	3	5.40	2.40	3.85	4.84
WAFER-PE1.2-4PWB-B4C	4	6.60	3.60	5.05	6.04
WAFER-PE1.2-5PWB-B4C	5	7.80	4.80	6.25	7.24
WAFER-PE1.2-6PWB-B4C	6	9.00	6.00	7.45	8.44
WAFER-PE1.2-7PWB-B4C	7	10.20	7.20	8.65	9.64
WAFER-PE1.2-8PWB-B4C	8	11.40	8.40	9.85	10.84
WAFER-PE1.2-9PWB-B4C	9	12.60	9.60	11.05	12.04
WAFER-PE1.2-10PWB-B4C	10	13.80	10.80	12.25	13.24
WAFER-PE1.2-11PWB-B4C	11	15.00	12.00	13.45	14.44
WAFER-PE1.2-12PWB-B4C	12	16.20	13.20	14.65	15.64

序号	品名	材质	MANUFACTURE DWG	东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd		
①	1.2 Pitch B型 2代电池座胶芯	LCP UL94 V-0, 颜色: 黑色	UNLESS OTHERWISE SPECIFIED TOLERANCES			
②	1.2 Pitch B型 2代电池座端子	铜合金/表面镀锡				
③	1.2 Pitch B型 2代电池座焊片	铜合金/表面镀锡				
			DECIMALS:	ANGLES:	TITLE: 1.20 Pitch B型卧式2代电池座	
			X.: ±0.30	±1°	PAR	WAFER-PE1.2-NPWB-B4C
			X.X: ±0.20		DWN	Lucas
			X.XX: ±0.10		CHKD	Ethan
					APVD	Jacob
					SCALE: 1:1	UNIT: MM
					SIZE: A4	SHEET: 1F1
					CUSTOMER COPY	REV: A