







技术指标:

- 1.温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 2.额定电流: 5.0A AC DC.
- 3.额定电压: 250V AC DC.
- 4.耐电压: 1000V AC/minute.
- 5.接触电阻: $\leq 20\text{m}\Omega$.
- 6.绝缘电阻: $\geq 1000\text{M}\Omega$.

材质:

- 1.胶芯: LCP UL94V-0 黑色
- 2.端子: 铜合金/表面镀锡
- 3.焊片: 铜合金/表面镀锡
- 4.不锈钢吸盖: 不锈钢


型号	CKT	A	B
WAFER-MX3.0-2PLB	2*1	0.00	6.65
WAFER-MX3.0-4PLB	2*2	3.00	9.65
WAFER-MX3.0-6PLB	2*3	6.00	12.65
WAFER-MX3.0-8PLB	2*4	9.00	15.65
WAFER-MX3.0-10PLB	2*5	12.00	18.65
WAFER-MX3.0-12PLB	2*6	15.00	21.65
WAFER-MX3.0-14PLB	2*7	18.00	24.65
WAFER-MX3.0-16PLB	2*8	21.00	27.65
WAFER-MX3.0-18PLB	2*9	24.00	30.65
WAFER-MX3.0-20PLB	2*10	27.00	33.65
WAFER-MX3.0-22PLB	2*11	30.00	36.65
WAFER-MX3.0-24PLB	2*12	33.00	39.65

PCB.WELDING DRAWING (TOLERANCE: ± 0.05)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: MX3.0MM 双排带扣立贴	
DECIMALS:	ANGLES:	PAR	WAFER-MX3.0-NPLB
X.X ± 0.30	X.* ± 5°	DWN	
X.XX ± 0.25	X.X* ± 1°	CHKD	
X.XXX ± 0.15		APVD	
CUSTOMER COPY		SCALE: A	UNIT: MM
		SIZE: A4	SHEET: 1F1
			REV: A

ROHS Compliant

MAPX	MODIFICATION	DATE	DRAW	APPROVE



MANUFACTURE DWG			东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: MX3.0MM 双排带扣立贴	
			PAR	WAFER-MX3.0-NPLB
			DWN	
			CHKD	
		APVD		
DECIMALS:		ANGLES:	SCALE:A	UNIT:MM
X.X±0.30		X.*±5°	SIZE:A4	SHEET:1F1
X.XX±0.25		X.X°±1°		REV:A
X.XXX±0.15				

CUSTOMER COPY