





MAPX	MODIFICATION	DATE	DRAW	APPROVE
序号	品名	材质		
①	4.2双排直针WTB嵌芯 4.2 double-row straight pin WTB connector insert	LCP UL94V-0 黑色 LCP UL94V-0 Black		
②	4.2双排立式WTB端子 4.2 Double-row Vertical WTB Terminal	铜合金/表面镀锡 Copper Alloy/Tin Plating		
③	4.2B型双排立式吸盖 Type 4.2B double-row vertical suction cap	不锈钢 stainless steel		

技术指标:


- 1.工作温度(Temperature range):-25°C~85°C.
- 2.额定电压(Rated voltage):250V AC,DC.
- 3.耐电压(Dielectricwithstanding voltage):1500V AC/minute.
- 4.接触电阻(Contact Resistance)20mΩ.
- 5.绝缘电阻(Insulation resistance):>1000MΩ.
- 6.额定电流(Rated voltage):7A AC,DC.


Part No	CKT	A	B
WAFER-MX4.2-4PLB	2X2	4.20	9.60
WAFER-MX4.2-6PLB	2X3	8.40	13.80
WAFER-MX4.2-8PLB	2X4	12.60	18.00
WAFER-MX4.2-10PLB	2X5	16.80	22.20
WAFER-MX4.2-12PLB	2X6	21.00	26.40
WAFER-MX4.2-14PLB	2X7	25.20	30.60
WAFER-MX4.2-16PLB	2X8	29.40	34.80
WAFER-MX4.2-18PLB	2X9	33.60	39.00
WAFER-MX4.2-20PLB	2X10	37.80	43.20
WAFER-MX4.2-22PLB	2X11	42.00	47.40
WAFER-MX4.2-24PLB	2X12	46.20	51.60

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 4.2B型双排立式WTB业务图	
DECIMALS:	ANGLES:	PAR	WAFER-MX4.2-NPLB
X.:±0.50	±1°	DWN	Lucas
X.X:±0.20		CHKD	Ethan
X.XX:±0.10		APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F2
			REV:A



PCB Layout





MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 4.2B型双排立式WTB业务图	
DECIMALS:	ANGLES:		PAR	WAFER-MX4.2-NPLB
X.:±0.50	±1°		DWN	Lucas
X.X:±0.20			CHKD	Ethan
X.XX:±0.10		CUSTOMER COPY		APVD Jacob
		SCALE:1:1	UNIT:MM	⌀
		SIZE:A4	SHEET:2F2	REV:A