


SPECIFICATION:

1.MATERIAL:

HOUSING:LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT:BRASS C2680R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u",3u",5u",15u"GOLD PLATING ON CONTACT AREA

100u" MIN.TIN PLATING ON SOLDER TAILS

40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:

CURRENT RATING:1.5 AMPERE PER CONTACT





CONTACT RESISTANCE:30 MILLIOHMS MAX

INSULATION RESISTANCE:1000 MEGOHMS MIN


DIELECTRIC WITH STANDING VOLTAGE:500 VDC

OPERATING TEMPERATURE: -40°C ~ +85°C

4.THE MARK (X) DIMENSIONS MUST BE MEASURED BY FAI.

PCB LAYOUT
TOLERANCES:±0.05MM

SECTION:Y-Y



SECTION:X-X

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE:SATA7+15P公座流板式SMT H0.9 (半包式)		
DECIMALS:	ANGLES:	PAR	SATA-15G-22ACB-H09	
.X:±0.30	.X':±3°	DWN	Lucas	
.XX:±0.20	.XX':±2°	CHKD	Ethan	
.XXX:±0.05	.XXX':±0.5°	APVD	Jacob	
CUSTOMER COPY		SCALE1:1	UNIT:MM	⌀
		SIZE:A4	SHEET:1F1	REV:A