


SPECIFICATION:

1.MATERIAL:

HOUSING: LCP/PA9T COLOR:BLACK

CONTACT:BRASS C2680R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:



CONTACT: 1u"/3u"/5u"/5u" GOLD PLATING ON CONTACT AREA

100u" MIN. TIN PLATING ON SOLDERTAILS


30u" MIN.NICKEL UNDERPLATING OVER ALL

PEG: 100u" MIN. TIN PLATING ON SOLDERTAILS



30u" MIN.NICKEL UNDERPLATING OVER ALL



SECTION A-A



PCB LAYOUT



SECTION B-B

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE:SATA 7P 公座B型 全包开窗鱼叉 侧插式针长2.05mm		
DECIMALS:	ANGLES:	PAR	SATA-02G-7AZZ-C16	
.X:±0.30	.X':±3°	DWN	Lucas	
.XX:±0.20	.XX':±2°	CHKD	Ethan	
.XXX:±0.05	.XXX':±0.5°	APVD	Jacob	
CUSTOMER COPY		SCALE1:1	UNIT:MM	Φ
		SIZE:A4	SHEET:1F1	REV:A