








SPECIFICATION:

1.MATERIAL:

HOUSING:LCP UL 94V-0

COLOR:BLACK

CONTACT:BRASS C2680-H,T=0.25mm

PEG:BRASS C2680R-H,T=0.30mm

2.FINISH:



CONTACT:1u"/3u"/5u"/15u" GOLD/TIN PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDER TAILS

50u" NICKEL UNDERPLATING OVERALL

PEG:100u" TIN PLATING ON SOLDER TAILS

50u" NICKEL UNDERPLATING OVERALL

RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Brass C2680R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE: SATA 7P 公座 三面电 SMT型		
DECIMALS:		ANGLES:		PAR
.X:±0.30		.X':±3°		SATA-03G-7AWB-H545
.XX:±0.20		.XX':±2°		DWN
.XXX:±0.05		.XXX':±0.5°		Lucas
CUSTOMER COPY		SIZE:A4		CHKD
		SHEET:1F1		Ethan
		REV:A		APVD
				Jacob