







ROHS Compliant



MAPX	MODIFICATION	DATE	DRAW	APPROVE
序号	品名	材质		
①	4.2A型双排立式WTB胶芯 4.2A Type Double-row Vertical WTB Housing	LCP UL94V-0 黑色 LCP UL94V-0 Black		
②	4.2A型双排立式WTB端子 4.2A Type Double-row Vertical WTB Terminal	铜合金/表面镀锡 Copper Alloy/Tin Plating		

技术指标:

- 1.工作温度(Temperature range):-25°C~85°C.
- 2.额定电压(Rated voltage):250V AC,DC.
- 3.耐电压(Dielectricwithstanding voltage):1500V AC/minute.
- 4.接触电阻(Contact Resistance)20mΩ.
- 5.绝缘电阻(Insulation resistance):≥1000MΩ.
- 6.额定电流(Rated voltage): 5A AC,DC.

Part No	CKT	A	B	C
WAfer-MX4.2F-4PLB	2X2	4.20	9.60	0.00
WAfer-MX4.2F-6PLB	2X3	8.40	13.80	4.20
WAfer-MX4.2F-8PLB	2X4	12.60	18.00	8.40
WAfer-MX4.2F-10PLB	2X5	16.80	22.20	12.60
WAfer-MX4.2F-12PLB	2X6	21.00	26.40	16.80
WAfer-MX4.2F-14PLB	2X7	25.20	30.60	21.00
WAfer-MX4.2F-16PLB	2X8	29.40	34.80	25.20
WAfer-MX4.2F-18PLB	2X9	33.60	39.00	29.40
WAfer-MX4.2F-20PLB	2X10	37.80	43.20	33.60
WAfer-MX4.2F-22PLB	2X11	42.00	47.40	37.80
WAfer-MX4.2F-24PLB	2X12	46.20	51.60	42.00

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

TITLE:

4.2A型双排立式WTB业务图

PAR

WAfer-MX4.2F-NPLB

DWN

Lucas

CHKD


Ethan

APVD

Jacob

SCALE1:1

UNIT:MM



CUSTOMER COPY

SIZE:A4

SHEET:1F2

REV:A

DECIMALS:


ANGLES:

X.:±0.50


±1°

X.X:±0.20


X.XX:±0.10




2*2




2*3




2*4




2*5




2*6




2*7




2*8




2*9



2*10



2*11



2*12

MANUFACTURE DWG			东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 4.2A型双排立式WTB业务图		
			PAR	WAFER-MX4.2F-NPLB	
DECIMALS:			DWN	Lucas	
X.:±0.50			CHKD	Ethan	
X.X:±0.20		APVD	Jacob		
X.XX:±0.10		SCALE 1:1	UNIT:MM		
		CUSTOMER COPY	SIZE:A4	SHEET:2F2	REV:A