




技术指标(Technical Index):

- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V DC/AC(rms).
- 3.额定电流(Rated current): 9.5A (AWG#16~#18) AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage):1500V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 7.适用线规(Apply to gauge):T1:AWG#16~#18.
T2:AWG#20~#24.

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: MX3.0公头端子(大电流)	
DECIMALS:	ANGLES:	PAR	WAFER-MX3.0-DZ-GD
X.: ± 0.50	$\pm 1^{\circ}$	DWN	Lucas
X.X: ± 0.20		CHKD	Ethan
X.XX: ± 0.10		APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A