

NOTES:

1.MATERIAL:

HOUSING:LCP 30% G/F UL94V-0

COLOR:BLACK

CONTACT:BRASS T=0.25mm

2.FINISH:

CONTACT:GOLD FLASH PLATING ON CONTACT AREA

100u"MIN.TIN PLATING ON SOLDERTAILS

50u"MIN.NICKEL UNDERPLATING OVER ALL

BOARD LOCK:100u"MIN.TIN PLATING ON SOLDERTAILS

50u"MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:








CURRENT RATING:1.5 AMPERE PER CONTACT

CONTACT RESISTANCE:30 mΩ MAX

INSULATION RESISTANCE:1000 MΩ MIN

DIELECTRIC WITH STANDING VOLTAGE:500 VDC

OPERATING TEMPERATURE: -40°C ~ +85°C

RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE:SATA 15P公座90度DIP型带 鱼叉针长2.30mm		
DECIMALS:	ANGLES:	PAR	SATA-01G-15BWZ-Z265	
.X:±0.30	.X':±3°	DWN	Lucas	
.XX:±0.20	.XX':±2°	CHKD	Ethan	
.XXX:±0.05	.XXX':±0.5°	APVD	Jacob	
CUSTOMER COPY		SCALE:1:1	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A