




SPECIFICATION:

1.MATERIAL:


HOUSING:LCP 30% G/F UL 94V-0
COLOR:BLACK
CONTACT:BRASS C2680R-H,T=0.25mm

2.FINISH:

CONTACT:1u",3u",5u",15u"30u"GOLD PLATING ON CONTACT AREA
100u" MIN.TIN PLATING ON SOLDER TAILS
40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:

CURRENT RATING:1.5 AMPERE PER CONTACT
CONTACT RESISTANCE:30 MILLIOHMS MAX
INSULATION RESISTANCE:1000 MEGOHMS MIN
DIELECTRIC WITH STANDING VOLTAGE:500 VDC
OPERATING TEMPERATURE: -40°C ~ +85°C



环保要求		产品必须符合ROHS要求		
2	Terminal	BRASS C2680R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE:SATA 7+15P 夹角公座 夹板 1.0七个孔		
DECIMALS:		PAR	SATA-07G-22BJB-J10	
ANGLES:		DWN	Lucas	
.X:±0.30		CHKD	Ethan	
.XX:±0.20		APVD	Jacob	
.XXX:±0.05		SCALE:1:1	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A