












RECOMMENDED PCB LAYOUT (TOLERANCE:±0.05)

■ PAD AREA
□ KEEP AREA
■ NO PATTERN AND VIA HOLE IN THIS AREA

NANO SIM CARD

Pin No.	ASSIGNMENT
C1	VCC(SUPPLY VOLTAGE)
C2	RST(RESET SIGNAL)
C3	CLK(CLOCK SIGNAL)
CD	Detect Switch
C5	GND
C6	VPP(VARIABLE SUPPLY VOLTAGE)
C7	I/O(DATA INPUT/OUTPUT)

NOTES :

1, MATERIAL SEE TABLE

2, ELECTRICAL PERFORMANCES :

2.1, CURRENT RATING :0.5A Max;

2.2, VOLTAGE RATING :30 V AC;

2.3, INSULATION RESISTANCE :100 MEGA OHMS MIN;

2.4, DIELECTRIC WITHSTANDING VOLTAGE:250V AC FOR 1 MINUTE;

2.5, CONTACT RESISTANCE :40 MILLI OHMS MAX ;

3, MECHANICAL PERFORMANCES :

3.1, CONTACT NORMAL FORCE :0.3N MIN. AT WORKING DEFLECTION;

3.2, DURABILITY :5000 CYCLES;

3.3, OPERATING TEMPERATURE : -40°C TO +85°C;

5	Lever	1	STAINLESS STEEL T=0.40	NO PLATING
4	Cam	1	STAINLESS STEEL T=0.40	NO PLATING
3	INSERT MOLDING	1	LCP UL94-V0	BLACK
2	CONTACT	7	COPPER ALLOY T=0.10	Au PLATED 1u"
1	SHELL	1	STAINLESS STEEL T=0.12	Au PLATED 1u"
NO	DESCRIPTION	QTY	MATERIAL	PLATING & COLOR

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co., Ltd

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:

.X: ±0.30 X.°: ±2°

.XX: ±0.20

.XXX: ±0.10

TITLE: NANO SIM Card
1.45H 7PIN 侧插卡托顶出式

PAR SMN-338-BRP7

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE: 1:1 UNIT: MM


SIZE: A4 SHEET: 1F2

REV: A


ITEM	W	A0	B0	K0	K0	E	F	D0	D1	P	P0	P2	T
DIM	24.00	6.00	5.00	7.00	7.00	1.75	11.50	1.50	1.00	4.00	12.00	2.00	0.30
TOLE	+0.30 -0.10	+0.10 -0.05	+0.10 -0.10	+0.10 -0.10	+0.10 -0.05	+0.10 -0.10	+0.10 -0.10	+0.15 -0.00	+0.10 -0.10	+0.10 -0.10	+0.21 -0.22	+0.23 -0.24	+0.25 -0.26

MAPX	MODIFICATION	DATE	DRAW	APPROVE


图示(一) 载带




图示(二) 圆盘包装



- NOTES:
- 1,每盘包装1300PCS产品。
 - 2,每箱包装数量14300PCS。纸箱外则以胶带封口成“工”字型。
 - 3,上载带剥离不速度: 300mm/minutes.
 - 4,卷带封合力小于100G。



1300pcsX11=14300pcs



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: NANO SIM Card 1.45H 7PIN 侧插卡托顶出式		
DECIMALS:		PAR SMN-338-BRP7		
ANGLES:		DWN Lucas		
.X: ±0.30		CHKD Ethan		
.XX: ±0.20		APVD Jacob		
.XXX:±0.10		SCALE1:1 UNIT:MM		
		SIZE:A4 SHEET:2F2 REV:A		