



Ass'y High(H)	Plastic High	
	Male (H1)	Female (H2)
1.50	1.14	1.45
2.00	1.14	1.95
2.50	1.14	2.40
3.00	1.14	2.90
3.50	1.14	3.40
4.00	1.14	3.90

SPECIFICATIONS:

- VOLTAGE/CURRENT RATING: 30V/AC, DC,0.3A;
- WITHSTANDING VOLTAGE: 100V AC/ONE MINUTE;
- INSULATION RESISTANCE: 50M Ω MIN/100V DC.;
- CONTACT RESISTANCE: 90m Ω MAX./1mA,20mV AC,1KHz;
- DURABILITY: 30 CYCLES;
- OPERATING TEMPERATURE RANGE: -40° C TO 125° C.

MATERIAL:

- INSULATOR: LCP UL 94V-0 BLACK;
- TERMINAL: PHOSPHOR BRONZE;

PLATING:

- TERMINAL: CONTACT AREA: GOLD 0.05 μ m"MIN.
SMT LEAD: GOLD 0.025 μ m" MIN.
UNDERPLATING: NICKEL 1 μ m" MIN.



PIN NO.	DIM A	DIM B	DIM C	DIM D
10	4.60	1.60	3.55	1.00
12	5.00	2.00	3.95	1.00
20	6.60	3.60	5.55	1.00
24	7.40	4.40	6.35	1.20
30	8.60	5.60	7.55	1.50
34	9.40	6.40	8.35	1.50
40	10.60	7.60	9.55	3.20
50	12.60	9.60	11.55	3.20
60	14.60	11.60	13.55	3.20
70	16.60	13.60	15.55	3.20
80	18.60	15.60	17.55	3.20
90	20.60	17.60	19.55	3.20
100	22.60	19.60	21.55	3.20
120	26.60	23.60	25.55	3.20

Ordering Information

HC-PBB40C - NDS - 0.4V - **

No of Pins	Nature DS=Female	PITCH	High (H)
10~120Pin		0.4V=0.4mm	1.5~1.50mm
12~120Pin			2.0~2.00mm
.....			2.5~2.50mm
			3.0~3.00mm
			3.5~3.50mm
			4.0~4.00mm

			GENERAL TOLERANCE		制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审 核 CHECK		产品名称 TITLE	0.4 双槽 立贴 母座 (BTB)	版 本 REV.	A
			X.X	±0.30	批 准 APPROVAL		产品料号 PART NO.	HC-PBB40C-NDS-0.4V-XX	单 位 UNITS	mm
			X.XX	±0.20	比 例 SCALE		材 料 MATERIAL		页 次 SHEET	1/2
1	初版发行		X.XXX	±0.10	投 影 Projection					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°						



			GENERAL TOLERANCE	制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审 核 CHECK				
			X. X ±0.30	批 准 APPROVAL	产品名称 TITLE	0.4 双槽 立贴 母座 (BTB) 包装图	版 本 REV.	A
			X. XX ±0.20	比 例 SCALE	产品料号 PART NO.	HC-PBB40C-NDS-0.4V-XX	单 位 UNITS	mm
1	初版发行		X. XXX ±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	2/2
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°					


深圳市华灿天禄电子有限公司
 ShenzhenhuacantianluELECTRONICS CO.,LTD