





ROHS



NOTE:

1.MATERIAL:

a.HOUSING:PBT UL 94V-0

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING:Ni=100u"-120u")

SEE ORDERING INFORMATION


2.ELECTRIC:

a.CONTACT RESISTANCE: 100 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTNIC VOLTAGE: 500V AC ONE SEC LEVEL

d.OPERATING TEMPERATURE: -25°C~ +85°C



3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20	Ni-Plating
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.40	Ni-Plating
1	HOUSING	1	PBT	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD		
DRAWING		TITLE 电池座适用电池规格CR2032 REV. A		
CHECK				
APPROVAL				
TOLERANCES ARE				
30-150	±0.35	ANGLE	PART NO. LAIL-CR2032-DIP90-B01-1AJ	
10-30	±0.2			
5-10	±0.15			
0-5	±0.1			
DWG.NO.			UNITS mm	
			Projection 	