

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PA66 UL94V-0

b.CONTACT:C5191

(SURFACE PLATING: Ni-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 50 MILLIOHMS MAX


b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE

d.OPERATING TEMPERATURE: -25°C~ +85°C

3.PACKAGING:

a.PLASTIC TRAY(PLEASE REFER TO PAGE TWO FOR DETAILS)

PCB Layout Diagram
BOTTOM View

3	TERMINAL(-)	1	C5191 T=0.3MM	Ni-Plating
2	TERMINAL(+)	1	C5191 T=0.3MM	Ni-Plating
1	HOUSING	1	PA66 UL94V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司		
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD		
CHECK					
APPROVAL					
TOLERANCES ARE					
30-150	±0.35	ANGLE	TITLE		
10-30	±0.2		电池底座适用电池规格CR1220		REV.
5-10	±0.15	±3°	PART NO.		
0-5	±0.1		LAIL-CR1220-DIP180-B01-1BJ		UNITS
			DWG.NO.		mm
			Projection 		