







PRODUCT NO.	DSWB06LHG1T
RohS compliant	



0.15±0.03



PCB Layout



- Note:**
1. All dimensions are in millimeters.
 2. General tolerance: ±0.2mm.
 3. Material:

Base: UL94V-0 PBT Thermoplastic (Black).
Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
Actuators: UL94V-0 PBT Thermoplastic (White).
Contact plating: Gold plating over nickel.
Pitting material: Epoxy.

4. Electrical


Electrical: 2000 Operations per switch 24/VDC, 25mA.
Non-Switching Rating: 100mA, 50/VDC.
Switching Rating: 25mA, 24/VDC
Contact Resistance: 100 mΩ Max. at initial.

5. Mechanical

Mechanical life: 2000 Operations per switch.
Stroke: 2.0mm.
Operation Temp: -20°C to 70°C.
Storage Temp: -40°C to 85°C.


6. PART NUMBER DESCRIPTION:

DS WB 06 L H G E T



注意:

1. 波峰焊: 推荐焊锡温度在270℃±5℃, 焊接时间为6~8秒。
2. 手工焊: 使用30瓦烙铁控制温度在320℃, 焊接时间大约2~3秒。
3. 波焊位置: 产品焊接时, 请将产品的波焊置于QFP端, 能给予产品更好的焊接性能。
4. 清洗过程: 清洗使用超声波方式, 能给予更好的效果。



TOLERANCE UNLESS OTHERWISE SPECIFIED				INSPECTION COPY			
LINER	ANGLES	PROJECTION	TITLE	FILE NO.	UNIT	SCALE	SHEET
0 ± 0.30	0 ± 1°	0 ± 0.5°	BY DSWB SERIES PITCH 2.54mm	DSWB06LHG1T-A	mm	FIT	1 OF 1
0.00 ± 0.10	0.00 ±	0.00 ±	PRODUCT FAMILY DSWB SERIES	DSWB06LHG1T	mm	FIT	1 OF 1
DESIGN	LU ER XIN	2013/07/02	PRAT NO.	DSWB06LHG1T	mm	FIT	1 OF 1
DRAWING					mm	FIT	1 OF 1
CHECK					mm	FIT	1 OF 1
APPRO.					mm	FIT	1 OF 1