




RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

4	GND
3	D+
2	D-
1	VBUS
PIN	NAME
PIN ASSIGNMENT	



GT-2A040F - S N N G0

Detail

F=No flanging no column

Shell Material

S=Stainless steel

Shell Plated

N=Ni

Housing Colour

W=White

N=Black

Terminal Plated

G0=G/F

G1=1u"

G3=3u"

G5=5u"

G-Switch USB-2.0 Specification:

- 1.Current rated: 2.0A
- 2.Voltage rating: 30V DC
- 3.Dielectric withstanding Voltage:500V AC
- 4.Contact resistance: 30mΩ Max
- 5.Insulation resistance: 1000MΩ Min
- 6.Operating temperature: -40°C ~ +85°C
- 7.Mating force: 3.57Kg Max
- 8.Unmating force: 1.02Kg Min
- 9.Durability cycle:5,000(SUS) cycles

1	SHELL	SUS304	NI PLATED
2	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK/WHITE UL 94V-0
3	TERMINALS	COPPER ALLOY C2680	G/F PLATED ON CONTACT AREA Tin PLATING ON SOLDER AREA
NO.	PARTS	MATERIAL	REMARKS



SCALE: 1:1	UNIT: mm	Title: Vertical USB 2.0 AF DIP H=10.0mm			
SIZE: A4		Molde Code: GT-2A040F-SNNG0			
Unless otherwise General Tolerance: X,x ±0.30 X,xx ±0.20 X,x° ±3°		DRAWN	CHECKED	APPROVED	DATE
		Xla	Chen	Chen	2024.03.10



REV: A0 SHEET: 1/1