






NO.	ECN NO.	DESCRIPTION	DATE



RECOMMENDED PCB LAYOUT

Note:

1: Material(材料) :

Housing: PA46 (胶芯: PA46)

Pin: Brass C6801 (针体: 无铅铜 C6801)

2: Plating(电镀) :

Pin: 3u' Au over 50~80u' Ni

针体: 镀金3u', 镍底50~80u'.

3: Electrical(电气特性) :

Insulation Resistance: 1,000MΩ minimum.

(绝缘电阻: 1,000MΩ以上)

Dielectric Withstand Voltage: 500VAC/minute.

(抗击电压: 500VAC/minute)

4: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: -40℃~ +85℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2024.3.28	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZT0044-18039-04025-02
CHECKED BY:		TITLE:	Pogo pin连接器
APPROVED BY:			