






NO.	ECN NO.	DESCRIPTION	DATE



RECOMMENDED PCB LAYOUT



Note:

- Material(材料):
Pin: Brass C3604 (针体: 黄铜 C3604)
Housing: PPA, White (胶芯: PPA, 白色, 无卤, 环保).
- Plating(电镀):
Pin: 3u' Au over 50~80u' Ni (针体: 镀金3u', 镍底50~80u'.)
- Electrical(电气特性):
Insulation Resistance: 1,000M Ω minimum. (绝缘电阻: 1,000M Ω 以上)
Dielectric Withstand Voltage: 500VAC/minute. (抗击电压: 500VAC/minute)
- WorkTemperture(工作环境):
Withstanding Higt Temperature: 280 $^{\circ}$ C
Operational Temperature: - 20 $^{\circ}$ C~ + 70 $^{\circ}$ C

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2022.3.4	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	± 0.05 mm	X.XX	$\pm 0.50^{\circ}$
X.X	± 0.10 mm	X.X	$\pm 1.00^{\circ}$
X.	± 0.20 mm	X.	$\pm 2.00^{\circ}$

DESIGNED BY:		DWG. NO.	YZT0664-20048-02028-01
CHECKED BY:		TITLE:	成品图
APPROVED BY:			