




客户图



RECOMMENDED PCB LAYOUT



Note:

- 1: Material(材料):
Housing: PA46+30%GF (胶芯: PA46 High temp.Plastic UL94 V-0 Color Black)
Pin: Brass C6801 (针体: 无铅铜 C6801)
- 2: Plating(电镀):
Pin: 5u' Au over 50~80u' Ni (针体: 镀金5u', 镍底50~80u'.)
- 4: WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: - 40℃~ +85℃
- 5: ALL PARTS MUST MEET TO RoHS REQUIREMENTS(所有物料及工艺必须符合R□HS 要求)

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2020.11.18	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZT0262-18027-08022-01
CHECKED BY:		TITLE:	POGO PIN连接器
APPROVED BY:			