


客户图



技术要求:

1. 材料:无铅铜C6801.
2. 不允许有批锋, 毛刺; 切断点最大不超过0.03mm.
3. 表面处理: 镀金3u', 铜底80-120u', 镍底120-200u';

深圳市鑫扬泽电子有限公司

[HTTP://WWW.XYZPOGOPIN.COM](http://www.xyzpogopin.com)

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2025.4.7	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	$\pm 0.05\text{mm}$	X.XX	$\pm 0.50^\circ$
X.X	$\pm 0.10\text{mm}$	X.X	$\pm 1.00^\circ$
X.	$\pm 0.20\text{mm}$	X.	$\pm 2.00^\circ$

DESIGNED BY:		DWG. NO.	YZT1170-20045-G3
CHECKED BY:		TITLE:	触点
APPROVED BY:			