




A



RECOMMENDED PCB LAYOUT

Note:

- 1: Material(材料) :
Housing: PA9T(胶芯:PA9T)
Pin: Brass C3604 (针体: 黄铜 C3604)
Magnet: NdFeB (磁铁: 钕铁硼)
- 2: Plating(电镀) :
Pin: 3u' Au over 50u'~80u' Ni
(针体: 镀金3u', 镍底50u'~80u'.)
Magnet : Nickel plating(镀镍)
- 3: Electrical(电气特性) :
Insulation Resistance: 1,000M Ω minimum.
(绝缘电阻: 1,000M Ω 以上)
Dielectric Withstand Voltage: 500VAC/minute.
(抗击电压: 500VAC/minute)
- 4: WorkTemperature(工作环境):
Withstanding Higt Temperature: 280 $^{\circ}$ C
Operational Temperature: - 20 $^{\circ}$ C~ + 70 $^{\circ}$ C