







ABIDE BY ROHS

TEM	H	
01	2.5	
02	2.8	
03	3.0	
04	3.5	
05	3.7	
06	4.0	
07	4.6	

* Key size



电路图




PCB. 焊接图

主要技术规格:

- 额 定 值: 50mA DC12V
- 接触电阻: $\leq 100m\Omega$
- 操 作 力: $260 \pm 50gf$
- 行 程: $0.20 \pm 0.1 mm$
- 绝缘电阻: $\geq 100M\Omega$
- 抗电强度: 250V 50HZ 1Min.
- 寿 命: 50,000 Cycles

材料:

本体: LCP (白色)
按钮: PPA (黑色)
卡件: 黄铜 (镀银)
弹片: 不锈钢
盖板: 黄铜 (镀银)



单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.			
绘图 DRAWN		>0.5~2	± 0.10	产品名称 TITLE	轻触开关		
设计 DESIGN		>2~5	± 0.25				
审核 CHECKED		>5~10	± 0.30				
图号 DRAWING NO		角度	$\pm 0.5^\circ$	产品型号 MODEL	3*4*H电子烟包脚		
校准化 STANDARD		重 量 WT.		产品编码 PART NO	ES317X-10XX-XXX-26-A		
批准 APPROVALS		产地 PRODUCTION		视角 PROJ		比 例 SCALE	: 页码 SHEET 1 OF 1